



1590-50PH in Fabric 629-70



1590-50PH in Fabric 629-70



1590-50PH in Fabric 629-70

FLEXSTEEL®


© Flexsteel Industries, Inc. | Last Updated 02/09/2024

| | |
|------|-----------------------|
| 50PH | FEATURES |
| ● | Flexsteel Spring Unit |
| | DualFlex |
| ● | Back Construction |
| | Attached |
| ● | Seat Construction |
| | Attached |
| ● | Seat Cushion(s) |
| | High-Density (HC) |

- Standard
- Optional

| PRODUCT DIMENSIONS | OVERALL | | | SEAT | | | Arm Height | Open Depth | Wall Clearance |
|--|---------|-------|-------|--------|-------|-------|---------------|---------------|-------------------|
| | Height | Width | Depth | Height | Width | Depth | | | |
| Power Recliner with Power Headrest & Lumbar -50PH | 43" | 38" | 42" | 19" | 23" | 21" | 25" | 71" | 6" |

Stocked Colors



Molasses
629-70
Fabric



Pumpernickel
629-72
Fabric

Printed samples may vary from actual swatches. Please refer to swatches for actual color.

NOTES

- Upholstery Material: Fabric
- Extended footrest.
- Removable backs allow for easy lifting and maneuvering through doorways.
- Power allows you to smoothly recline to any position, adjust the headrests, and adjust the lumbar supports.
- A single USB port is included on each power button control on styles with arms.
- A home feature returns the headrest, footrest, and lumbar support to their original positions.



Home Button
The home button returns the headrest, footrest, and lumbar support to their original positions. To activate the home button, press and hold the button used to lower the footrest.



MyRecline F4 Mobile App
Download the free MyRecline F4 app to program memory positions and use your device as a wireless remote control.