



2810-50 in fabric 407-30



2810-50 in Fabric 936-40

$F L E X S T E E L^{\circ}$

2810-50 in Fabric 936-40

© Flexsteel Industries, Inc. | Last Updated 02/01/2024

Arlo | 2810

53 51M	FEATURES	PRODUCT DIMENSIONS	OVERALL			SEAT					
51N 51L 51H 50 50L 50L 50H 50			Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
		Swivel Gliding Recliner -53	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Flexsteel Spring Unit DualFlex	Power Rocking Recliner -51M	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Back Construction Attached	Power Rocking Recliner with Power Headrest & Lumbar -51L	43"	37"	42"	20"	21"	22"	27"	70"	13"
•	Seat Construction Attached	Power Rocking Recliner with Power Headrest -51H	43"	37"	42"	20"	21"	22"	26"	70"	13"
•	Seat Cushion(s) High-Density (HC)	Rocking Recliner -51	43"	37"	42"	20"	21"	22"	26"	70"	13"
0	Tailoring Arm Covers	Power Recliner -50M	43"	37"	42"	20"	21"	22"	26"	70"	8"
		Power Recliner with Power Headrest & Lumbar -50L	43"	37"	42"	20"	21"	22"	27"	70"	8"
• Standard o Optional		Power Recliner with Power Headrest -50H	43"	37"	42"	20"	21"	22"	26"	70"	8"
		Recliner -50	43"	37"	42"	20"	21"	22"	26"	70"	8"

NOTES

Handle-activated recline system on the side of the arm allows you to manually adjust between sitting and reclining Pull-fuffed, triple-divide back cushions support your back and have distinctive look. Rounded pad-over track arms enhance confort and provide additional forearm support developments and the support of the support development of the support of the support of the support addition and durability. Cushions consist of a high-resiliency, high-density polyurethane form core with a soft fiber wrap that ensures confort as you sit and recline. Available in our 250 fabrics to suit any decore fabrics that will withstand everyday use by an active family Available in our 250 fabrics to suit any decore in a down and more support and maneuvering through downays Footrest easily lowers when you apply pressure in a downaved motion Swidel mechanism allows searnless adde-to side motion Swidel mechanism allows searnless adde to see Power control on the arm independently adjusts the recline, keeping you comfortable USB charging port built into pendently adjusts the headrest and recline for a personalized sit Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recline. New all USB port is included on each power button control on styles with arms. The power control allows you to independently adjust the recline, headrest, and lumbar support. A separate home button returns the headrest, footrest, and lumbar support. A separate home button returns the hea



Power Recline, Headrest, & Lumbar



Power Recline & Headrest

FABRIC

FLEXSTEEL®