



Power Rocking Recliner 2900-51M in 145-01



© Flexsteel Industries, Inc. | Last Updated 10/26/2023

Power Rocking Recliner 2900-51M in 145-01

2900-51M in fabric 145-01

$F L E X S T E E L^{\circ}$

Catalina | 2900

Catalina | 2900

53 51M		PRODUCT DIMENSIONS	OVERALL		SEAT						
51H 51 50M 50H 50	Flexsteel Spring Unit DualFlex Back Construction Attached Seat Construction Attached		Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
		Swivel Gliding Recliner -53	40"	34"	40"	19"	22"	21"	24"	65"	13"
		Power Rocking Recliner -51M	40"	34"	40"	19"	22"	21"	24"	65"	13"
		Power Rocking Recliner with Power Headrest -51H	40"	34"	40"	19"	22"	21"	24"	65"	13"
		Rocking Recliner -51	40"	34"	40"	19"	22"	21"	24"	65"	13"
	Seat Cushion(s) High-Density (HC)	Power Recliner -50M	40"	34"	40"	19"	22"	21"	24"	65"	5"
o		Power Recliner with Power Headrest -50H	40"	34"	40"	19"	22"	21"	24"	65"	5"
		Recliner -50	40"	34"	40"	19"	22"	21"	24"	65"	5"

Standard

o Optional

NOTES

A clean, transitional design

Padded, soft sloped track arms Gently rocks when not reclined and has safety locks to prevent rocking when reclined

Adjust from an upright to a fully reclined position with the touch of a button Charge electronic devices with the dual USB-A port located in the power

button

Sustainably sourced wood frame delivers exceptional durability

Contoured, high-density foam seat cushion provides lasting, everyday comfort and support

Upholstered in your choice of more than 250 select fabrics, including those with performance and sustainability characteristics

Handcrafted in North America

Swivels a full 360 degrees and allows you to glide or recline from any swivel position

Gently glides when not reclined and has safety locks to prevent gliding when reclined

Adjust from an upright to a fully reclined position by pulling back on the side handle in the arm

Adjust the recline and headrest positions with the touch of a button Charge electronic devices with the single USB-A port located in the power button

Power allows you to smoothly recline to any position.

A single USB port is included on each power button control on styles with arms.

Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recliner.

The power control allows you to independently adjust the recline and headrest. A separate home button returns the headrest and footrest to their original positions with one touch.

A USB port is included on the power control for powering electronics. Zero draw technology only uses power when the USB port is in use.



Power Recline & Headrest