




Power Recliner 2904-50M in 440-02

Power Recliner 2904-50M in 440-02

## FLEXSTEEL°

© Flexsteel Industries, Inc. | Last Updated 04/08/2024



## **Rio** | 2904

53 51			PRODUCT DIMENSIONS	OVERALL		SEAT						
51 51 50	H I MC	FEATURES		Height	Width	Depth	Height	Width	Depth	Arm Height	Open Depth	Wall Clearance
50H 50		Flexsteel Spring Unit DualFlex Back Construction Attached Seat Construction Attached	Swivel Gliding Recliner -53	42"	38"	41"	19"	21"	21"	24"	68"	14"
	•		<b>Power Rocking Recliner</b> -51M	42"	38"	41"	19"	21"	21"	24"	68"	14"
•	•		Power Rocking Recliner with Power Headrest -51H	42"	38"	4]"	19"	21"	21"	24"	68"	14"
	•		Rocking Recliner -51	42"	38"	41"	19"	21"	21"	24"	68"	14"
	•	Seat Cushion(s) High-Density (HC)	Power Recliner -50M	42"	38"	41"	19"	21"	21"	24"	68"	4"
	0		Power Recliner with Power Headrest -50H	42"	38"	41"	19"	21"	21"	24"	68"	4"
			<b>Recliner</b> -50	42"	38"	41"	19"	21"	21"	24"	68"	4"

Standard

o Optional

## NOTES

Power control on the arm effortlessly adjusts the recline, keeping you comfortable USB charging port built into power control keeps devices powered up and ready to use Divided back cushion cradles your neck, back and lower lumbar for enhanced comfort Streamlined inset padded armrests have a seamless look and comfortable feel Built to last with our patented Flexsteel DualFlex Spring System™-sturdy steel ribbons attached to flexible coils that offer a wide range of motion and durability High-density cushions consist of a high-resiliency, high-density polyurethane foam core

with a soft fiber wrap that ensures comfort as you sit and recline Available in over 250 fabrics to suit any décor

Available in durable, cleanable performance fabrics that will withstand everyday use by an active family

Removable back allows for easy lifting and maneuvering through doorways Swivel mechanism allows seamless side-to-side motion

Gliding mechanism provides soothing movement that helps you relax

Handle-activated recline system on arm allows you to manually yet efficiently move between sitting and reclining

Footrest easily lowers when you apply pressure in a downward motion Rocking recliner provides soothing movement in the seated position, helping you relax Home button returns the headrest and footrest to their original positions with one touch Power allows you to smoothly recline to any position.

A single USB port is included on each power button control on styles with arms. Lower the footrest by applying pressure to it in a downward motion. Lowering the footrest with the handle can damage the recliner.

The power control allows you to independently adjust the recline and headrest. A separate home button returns the headrest and footrest to their original positions with one touch.

A USB port is included on the power control for powering electronics. Zero draw technology only uses power when the USB port is in use.



**Power Recline** & Headrest

## F L E X S T E E L<sup>®</sup>